



Product Datasheet

ENGLISH

**Stock No: 123-1933, 1231933, 1231966,
1231967 & 1231968**

RS PRO Phase Rotation Indicator

EN



Features

Nominal voltage: 40V to 690V AC

Frequency range: 15 to 400Hz

Current pickup: 1mA

Nominal test current(per phase): 1mA

Power supply: From unit under test

Electrical safety: IEC61010/EN61010; IEC61557-7/EN61557-7

Protection level: CATIII 600V

Type of protection: IP40

Operating temperature: 0°C to 40°C

3 Phase indication

Indication of phase rotation

Clear LCD display

No battery required

Specifications

Environmental

Operating Temperature: 0°C to +40°C

Pollution Degree: 2

Type of protection: IP40

Mechanical Specifications

Size:(H x W x D): 130mm x 69mm x 32mm.

Weight: 130g

Safety Specifications

Electrical Safety:

IEC 61010 / EN61010,

IEC 61557-7 / EN 61557-7

Maximum Operating Voltage (Ume):690 V

Protection Levels:CAT III, 600V to ground

Electrical Specifications

Power Supply: From unit under test

Determine Rotary Field Direction

Nominal Voltage: 40 to 690 VAC

Frequency Range (fn): 15 to 400HZ

Current pickup: 1 mA

Nominal Test current (in per phase): 1 mA

Accessories:

3 pieces self-retaining test leads, 3 alligator clips, User Manual and gift box with carrying case.