



ENGLISH

Datasheet

Stock No. 123-2233

RS-1364

Humidity / Temperature Meter



FEATURES

- Dual LCD with Bargraph Display for RH% Humidity, Air Temperature.
- Dew Point Reading.
- Wet Bulb Reading.
- Max / Min with Time Stamp.
- Data Hold & Relative function.
- Auto Power Off function.
- DATA Memory and Read function. (99 readings from LCD display)

SPECIFICATIONS

Measuring Range	Temperature : -20 to 60°C (-4 to 140°F) Humidity : 10%RH to 95%RH
Resolution	0.1°C/0.1°F/0.1%RH
Accuracy	Temperature : $\pm 0.5^{\circ}\text{C}$, $\pm 0.9^{\circ}\text{F}$ Humidity : $\pm 3\% \text{RH}$ (at 25°C, 30 to 95% RH). $\pm 5\% \text{RH}$ (at 25°C, 10 to 30% RH).
Data Memory capacity	Manual recording : 99 data sets. (Direct reading from LCD display)
Sampling Rate	2 times per second
Operation Temperature & Humidity	0 to 60°C, below 95% RH. (no condensation)
Storage Temperature & Humidity	-10 to 60°C, below 70% RH.
Power Source	6 pcs size AAA Battery
Battery Life	Approx. 160 hours.
Size	150x72x35 mm
Weight	Approx. 235g
Accessories	Instruction manual, Battery and case.