

Datasheet Foot switch, DPDT



RS Article No.1253710

Specifications:

Operating Frequency:	60 ops/min
Insulation Resistance:	>100M Ω @500V DC
Contact Resistance:	<25m Ω (initial)
Rated Current/Voltage:	20A 125VAC/250VAC/480VAC 1.5HP/125VAC,2HP/250VA
Dielectric Strength:	1000VAC for 1 min between current carrying parts
	2500VAC for 1 min between non-current carrying parts
Service Life:	Mechanically 1X10 ⁶ Electrically 5X10 ⁵
Operating Temperature:	-20~+80°C (-4~176°F)
Degree of Protection:	IP65
Size (LXWXH):	228X157X140mm

Features:

- Treadle and housing constructed from cast iron for strength and durability
- Strong cast aluminium guard construction
- Anti-skid rubber feet and three holes for rigid mounting to floor or equipment
- UL/CSA/CE/CCC Certified
- DPDT TYPE
- Momentary type
- M20 Conduit type

