




## **Datasheet**


## **Connector Assembly**

RS Stock 877-1012



## **Dimensions: (mm)**





RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.





## **Specifications**

<b>General Specification</b>	
Rated Operational Voltage	60 V
Current Rating	4A
Insulation Resistance	>= 100 MΩ
Temperature Range	-25°C +75°C
Degree of Protection	IP67

Material Specification	
Grip Material	PU
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
Grip Colour	Black
Coupling Nut	Brass Nickel-Plated

Cable Specification	
Cable Length-L	2 m
Cable Type	3 Core PVC Multi Strand
Sheath Colour	Black
Cross Section of Wire	0.34 sq. mm
Core Dia	1.4 mm
Cable Dia	4.5 ± 0.1 mm
Termination	Partially Stripped