



LED/Multiled	<i>LED</i>	Optimum voltage (V)	12Vdc	Intensity	1300mcd@20mA
Mounting Size	14mm	Rectifier			
Mounting Finish	<i>Chrome Bezel</i>	AC current			
Protection	<i>IP67</i>	DC current	20mA (max)		
Mount Holder	<i>Prominent</i>	Voltage Tolerance (%)	10%		
Chip Qty	1	Optimum temperature (°C)	-30°C...+65°C		
Indicator colour	Yellow	Storage temperature (°C)			
Wavelength (nm)	589	Contact Tab x 2	2,8x0,8		



Dimension in mm (typical), not to scale. We reserve the right to make changes without further notice to this product to improve reliability, function or design.