



Scotch® Vinyl Electrical Color Coding Tape 35-Blue-3/4, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

UPC# 00054007108368 3M Product Number 35-BLUE-3/4 3M ID 80610833925

This blue, 7 mil premium grade electrical vinyl tape stretches to conform to virtually any shape that requires color-coded insulation. Inner pack of 1 per canister, 10 per carton with 100 rolls per case.



Overview Support

Scotch® Vinyl Electrical Color Coding Tape 35 is used in phase identification, color coding leads and piping systems and for marking safety areas. This tape is abrasion- and weather-resistant, with excellent mechanical and electrical insulation properties.

Specifications

| | |
|---|---|
| Adhesive Material | Rubber Resin |
| Agency Approvals | UL Listed, CSA Certified, VDE 0340-TEIL1 |
| Backing Material | Polyvinyl Chloride |
| China RoHS - Below MCV | Yes |
| Dielectric Strength | 1250 Millivolt |
| EU RoHS Compliant | Yes |
| Length | 66 Linear Foot |
| Maximum Operating Temperature (Celsius) | 105 Degree Celsius |
| Operating Temperature Range | 0 to 105 Degree Celsius |
| Product Family | Scotch® Vinyl Color Coding Electrical Tape 35 |
| Product Type | Vinyl Tape |
| Tape Color | Blue |
| Tape Grade | Professional |
| Tape Length | 66 Linear Foot |
| Tape Total Thickness | 7 Milli-inch |
| Tape Total Thickness (metric) | 0.177 mm |
| Tape Type | Vinyl Electrical |
| Tape Width | 0.75 in |
| Thickness | 7 Milli-inch (mil) |
| Width | 3/4 Inch |