	8	7	6	5	★ 4	3	2	1	
	THE INFORMATION CONTAIN PROPERTY OF L-COM, INC. AI WITHOUT THE WRITTEN PERMISS	ED IN THIS DRAWING IS THE SOLE NY REPRODUCTION IN PART OR WHOLE SION OF L-COM, INC. IS PROHIBITED.				REV B RELEASED FOR PRODUCT B REVISED TOLERANCES PE C ECN 3131: UPDATE DWG	R ECN 1489	DATE 11/19/01 08/08/03 12/28/07	CHANGED BY MCCORMICK MCCORMICK D.GRIFFIN
D								12/20/07	
				1.6[39.4]					-
С								1.3[32.1]	(
*		2X BNC JACK					BNC PLUG		•
В									E
	SPECIFICATIO MATERIALS; SHELL: BRASS INSULATOR: D								
A	FINISH; Shell: Nickel Contact: G(Electrical;	- PLATED			RoHS Con UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm TOLERANCES TO BE: X ± 11 [2:5] X ± 10 [2:5] X ± 005 [.13] OVERALL CABLE LENGTH TOL: < 60 [1524] + 376.2] / -0	MCCORMICK 11/14/01		5 BEECHWOOD IORTH ANDOVEI 01845 DAXIAL FOR BNC M/F BA845	R, MA
	8	7	6	5	▲ 4	3	2	1	UNILLI I UF I