



Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Superprox 900
Device short name	SM952
Sensor design	Cylindrical M30
[Sn] nominal sensing distance	3.28 ft (1 m)
Type of sensing window	Adjustable
Material	Plastic
Enclosure material	ULTEM
Front material	Silicone rubber
Type of output signal	Discrete
Discrete output function	1 NO
ISO thread	M30 x 1.5
Wiring technique	4-wire
[Us] rated supply voltage	12...24 V DC (overload and short-circuit protection)
Supply voltage limits	10...28 V DC
Discrete output type	NPN
Electrical connection	1 male connector M12 4 pins
Product specific application	Dual-level - setpoint

Complementary

[Sd] sensing range	0.17...3.28 ft (0.0508... 1 m)
Maximum differential travel	0.1 in (2.5 mm)
Blind zone	2.01 in (51 mm)
Transmission frequency	200 kHz
Repeat accuracy	0.87 %
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 1.6 mm - up to 305 mm sensing distance
Current consumption	100 mA
Maximum switching current	100 mA (reverse polarity protection)
Height	1.18 in (30 mm)
Width	1.37 in (34.7 mm)
Depth	1.18 in (30 mm)
Length	3.78 in (96 mm)
Product weight	0.57 lb(US) (0.26 kg)

Environment

product certifications	UL
marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
ambient air temperature for operation	32...122 °F (0...50 °C)
ambient air temperature for storage	-4...176 °F (-20...80 °C)
relative humidity	100 % without condensation
vibration resistance	+/-1 mm conforming to IEC 60068-2-6 10...55 Hz
shock resistance	30 gn in all 3 axes 11 ms conforming to IEC 60068-2-27
resistance to electromagnetic fields	9.14 V/yd (10 V/m) (level 3) conforming to IEC 61000-4-3

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

resistance to fast transients

1 kV (level 3) conforming to IEC 61000-4-4

Contractual warranty

Warranty period

18 months
