

# Rittal – The System.

Faster – better – everywhere.

## ► Hygienic Design Command panel HD – HD 4000.062

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Hygienic Design Command panel HD – HD 4000.062

created: 19.03.2018 build on [www.rittal.com/us-en](http://www.rittal.com/us-en)



The product is used in industry/IT projects.

## Product description

<b>Version:</b>	Roof slope 30° towards the front
<b>Benefits:</b>	Roof slope 30° towards the front Height-adjustable mounting board for screens up to 24" in size Bracket for TFT table height adjustable for screens up to 24"
<b>Material:</b>	Housing and door: Stainless steel 1.4301 (AISI 304) Lock inserts HD: Stainless steel 1.4404 (AISI 316L) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
<b>Surface finish:</b>	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
<b>Protection category IP to IEC 60 529:</b>	IP 66
<b>Protection category IP to DIN 40 050-9:</b>	IP 59K
<b>Supply includes:</b>	Housing of all-round solid construction Door with viewing window and inserted seal R/h door catch Holder for desktop TFT with VESA 75/100 locator
<b>Options:</b>	without viewing window Mounting plate instead of mounting board Cut-out for touch panel instead of viewing panel Keyboard Support HD

## Product features

<b>Dimensions:</b>	Height (front): 692 mm (27 ") Height (rear): 848 mm (33 ") Width: 810 mm (32 ") Depth: 266 mm (10 ")
<b>Viewing Windows:</b>	Height: 325 mm (13 ") Width: 535 mm (21 ")
<b>Material thickness::</b>	Housing: 1.5 mm (0.06 ") Door: 2 mm (0.08 ")
<b>Packaging unit:</b>	1 pc(s).
<b>Weight/packaging unit:</b>	33.2 kg (73.2 lb.)
<b>EAN:</b>	4028177709539
<b>Customs tariff number:</b>	94032080
<b>ETIM 6.0:</b>	EC000261
<b>ETIM 5.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 7.0/7.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>eCl@ss 5.1/5.1.4:</b>	27180102