


Angle seat valve

VZXF-L-M22C-M-B-G2-430-H3B1-50-3-EX4

Part number: 3540293

FESTO



Data sheet

Feature	Value
Design structure	Poppet valve with spring return
Type of actuation	pneumatic
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	G2
Nominal diameter DN	50
Nominal size	43 mm
Valve function	2/2 closed, monostable
Flow direction	non reversible
Medium pressure	0 ... 3 bar
Nominal pressure of process valve	16
Exhaust-air function	not throttleable
Type of reset	mechanical spring
Type of piloting	With external control
Pneumatic connection	G1/8
Working pressure	6 ... 10 bar
Medium	Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 µm Neutral fluids
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Max. viscosity	600 mm ² /s
Medium temperature	-10 ... 80 °C
Ambient temperature	-10 ... 60 °C
Flow rate Kv	23 m ³ /h
Materials note	Contains PWIS substances Conforms to RoHS
Material housing	Gunmetal (red brass)
Material number for housing	CC499K
Material drive head	Brass
Material spindle seal	NBR
Material seat seal	PTFE
Product weight	2,800 g
ATEX category Gas	II 2G
Explosion ignition protection type Gas	c TX X
ATEX category Dust	II 2D
Explosion ignition protection type Dust	c TX X
Explosion-proof ambient temperature	-10 °C ≤ Ta ≤ +60 °C
CE symbol (see declaration of conformity)	according to EU printing device guideline according to EU-Ex protection guideline (ATEX)
Corrosion resistance classification CRC	1 - Low corrosion stress