



Shut-off valve HE-N3/4-LO

Part number: 197131

FESTO



Data sheet

Feature	Value
Sealing principle	soft
Exhaust-air function	not throttleable
Type of piloting	direct
Working pressure	1 ... 10 bar
C value	36.28 l/sbar
b value	0.21
Standard nominal flow rate	8,000 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Corrosion resistance classification CRC	3 - High corrosion stress
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Mounting type	Threaded
Assembly position	Any
Flow direction	non reversible
Product weight	1,000 g
Pneumatic connection, port 1	NPT3/4-14
Pneumatic connection, port 2	NPT3/4-14
Pneumatic connection, port 3	NPT3/4-14
Pneumatic connection, port 5	NPT3/4-14
Material seals	NBR TPE-U(PU)
Material housing	Aluminum die cast