



Connecting cable SIM-M8-3GD-10-PU

Part number: 192964

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 61076-2-104 EN 61984
Ready status display	Green LED
Electrical connection	Straight socket/open end M8x1 / - 3-pin/3-wire
Operating voltage range DC	0 ... 60 V
Operating voltage range AC	0 ... 60 V
Acceptable current load at 40 °C	3 A
Surge strength	1.5 kV
Cable length	10 m
Cable attribute	Standard
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm
Cable structure	3x0,25
Nominal conductor cross-section	0.25 mm ²
Color code, core insulation	blue brown Black
Protection class	IP65 IP68
Ambient temperature	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Materials note	Free of copper and PTFE Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PU)
Cable sheath color	Grey
Material housing	TPE-U(PU)
Housing color	Black
Material of union nut	Brass Nickel plated
Material insulation	PVC