



# Connecting cable SIM-M8-4WD-2,5-PU

Part number: 158962

FESTO



## Data sheet

Feature	Value
Conforms to standard	EN 61076-2-104 EN 61984
Electrical connection	Angled socket/open end M8x1 / - 4-pole / 4-wire
Operating voltage range DC	0 ... 30 V
Operating voltage range AC	0 ... 30 V
Acceptable current load at 40°C	3 A
Surge strength	0.8 kV
Cable length	2.5 m
Cable attribute	Standard
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm
Cable structure	4x0,25
Nominal conductor cross-section	0.25 mm <sup>2</sup>
Color code, core insulation	blue brown Black white
Protection class	IP65 IP68
Ambient temperature	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
Materials note	Free of copper and PTFE Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PU)
Cable sheath color	Grey
Material housing	TPE-U(PU)
Housing color	Black
Material of union nut	Brass Nickel plated
Material insulation	PVC