


Electrical module VMPA2-FB-EMS-D2-4

Part number: 543332

FESTO



Data sheet

Feature	Value
Diagnosis	<ul style="list-style-type: none">- Condition Monitoring- Wire break per solenoid coil- Short circuit of valves- Undervoltage of valves
Max. number of valve positions	2
Max. number of solenoid coils	4
Intrinsic current consumption at load voltage	3 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal breakaway current per solenoid coil	99 mA up to 24 ms
Nominal current with current reduction	18 mA after 24 ms
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
Product weight	20 g
Material housing	POM
Materials note	Conforms to RoHS