


# Electrical module VMPA1-FB-EMG-D2-8

Part number: 543333

FESTO



## Data sheet

Feature	Value
Diagnosis	- Condition Monitoring - Wire break per solenoid coil - Short circuit of valves - Undervoltage of valves
Max. number of valve positions	4
Max. number of solenoid coils	8
Intrinsic current consumption at load voltage	23 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal breakaway current per solenoid coil	58 mA up to 24 ms
Nominal current with current reduction	9 mA after 24 ms
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
Product weight	20 g
Material housing	POM
Materials note	Conforms to RoHS