



Vacuum generator VAD-ME-I-1/4

Part number: 35532
Classic

FESTO

With integrated solenoid valve for vacuum On/Off and ejector pulse

Unlubricated air is recommended.



Data sheet

Feature	Value
Nominal size, Laval nozzle	1.4 mm
Assembly position	Any
Ejector characteristic	High vacuum
Integrated function	Ejector pulse valve, electrical Electrical on-off valve
Design structure	T-shaped
Working pressure	1.5 ... 8 bar
Max. vacuum	90 %
Duty cycle	100%
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Medium temperature	0 ... 50 °C
Protection class	IP65
Ambient temperature	0 ... 50 °C
Electrical connection	Plug
Mounting type	with internal (female) thread
Pneumatic connection, port 1	G1/8
Vacuum connection	G1/4
Material housing	Aluminum