



# Pressure switch PEV-1/4-B-OD

Part number: 175250

FESTO



## Data sheet

Feature	Value
Conforms to standard	EN 60947-5-1
Authorization	CCC
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Materials note	Conforms to RoHS
Measured variable	Relative pressure
Measurement method	Pneu./elect. pressure transducer
Working pressure	1 ... 12 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Medium temperature	-20 ... 80 °C
Ambient temperature	-20 ... 80 °C
Switching element function	Changeover switch
Max. switching frequency	3 Hz
Max. switching output voltage AC	250 V
Max. switching output voltage DC	125 V
Max. output current	5,000 mA
Minimum load current	1 mA at 24 V 10 mA at 10 V 100 mA at 5V
Utilization category for inductive load	AC-14 DC-13
Utilization category for ohmic load	AC-12 DC-12
Electrical connection	Plug Cubic design to DIN 43650 Plug pattern type A to EN 175301-803
Mounting type	with through hole
Assembly position	Any
Pneumatic connection	G1/4
Product weight	194 g
Material housing	Aluminum die cast
Material switch contact	silver
Operating status display	Yellow LED
Threshold setting range	1 ... 12 bar
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress