


Part number: 192009



## **Data sheet**

Feature	Value
Based on the standard	EN 61076-2-101
	EN 61984
Mounting type	with threaded sleeve
Assembly position	Any
Product weight	11 g
Electrical connection	M8x1
	3-pin
	Straight plug / screw terminal
Operating voltage range DC	<= 60 V
Operating voltage range AC	<= 60 V
Acceptable current load at 40°C	3 A
Surge strength	1.5 kV
Cable gland connection	Pg7
Permissible cable diameter	2.5 5 mm
Terminal cross-section	0.14 0.5 mm2
Protection class	IP65
Ambient temperature	-40 85 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material housing	PA
Housing color	Black
Material of union nut	Brass
	Chromed-plated
	Nickel plated
Material electrical contact	Brass
	Gold plated