


Push-in fitting QBM-10-32-UNF-1/4-U

Part number: 573050

FESTO



Data sheet

Feature	Value
Size	Mini
Nominal size	0.098 "
Type of seal on screw-in stud	Sealing ring
Assembly position	Any
Design structure	Push/pull principle
Operating pressure complete temperature range	-13.8 ... 145 Psi
Temperature dependent working pressure	-13.8 ... 145 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	32 ... 140 °F
Max. tightening torque	1.106 ft-lbf
Product weight	0.353 oz
Pneumatic connection, port 1	Male thread UNF10-32
Pneumatic connection, port 2	for tubing, 1/4" outside diameter
color of release ring	Grey
Materials note	Contains PWIS substances Conforms to RoHS
Material housing	Nickel-plated brass PBT
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive