


Connecting cable KVI-CP-3-WS-WD-5

Part number: 540330

FESTO



Data sheet

Feature	Value
Additional functions	Contact 3 of socket 1 mm leading
Cable identification	with accessories
Connection frequency	500
Product weight	257.8 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M9x0,5
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	M9x0,5
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Electrical connection 2, type of mounting	Screw lock
Operating voltage range DC	0 ... 30 V
Acceptable current load at 40°C	1.6 A
Note on acceptable current load at 40°C	2.3 A for 0.34 mm ² 3.6 A for 0.49 mm ²
Surge strength	1.5 kV
Cable length	5 m
Cable attribute	Suitable for chain link trunking
Test conditions of cable	Test conditions on request
Bending radius, flexible cable installation	>= 75 mm
Cable diameter	5.5 mm
Cable structure	2x0,25+2x0,34+0,49 Shielded
Nominal conductor cross-section	0.25 mm ² 0.34 mm ² 0.49 mm ²
Protection class	IP65 IP67
Note on degree of protection	in assembled condition
Ambient temperature	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
Materials note	Conforms to RoHS
Degree of contamination	1
Corrosion resistance classification CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)

Feature	Value
Cable sheath color	light grey
Material housing	PA PBT TPE-U(PUR)
Housing color	Black
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	TPE-U(PUR)