



# IP710-DLZ

## Brand Features

Leviton offers many products that will help lower electrical costs and add convenience to everyday living. By simply replacing standard switches with dimmers reduces energy consumption and extends bulb life. IllumaTech Preset Dimmers and Fan Speed Controls feature a low-profile fluid slide bar movement for fine adjustment of light levels or fan speeds that's accompanied by an easy-to-use ON/OFF preset switch. The switch provides quick ON/OFF control without disturbing your favorite pre-selected settings. Most feature a built-in LED locator light, as well. Models are available for incandescent, magnetic or electronic low-voltage, and Mark 10 Powerline dimming-ballast fluorescent lighting, and quiet and standard fan speed control.

## Item Description

1200VA, 120/277 Volt AC 60Hz, Single-Pole & 3-Way, IllumaTech Preset Electro-Mechanical Electronic 0-10VDC Fluorescent Slide Dimmer, LED Locator Light, Suitable for use with Class 1 or Class 2 wiring - White face assembled on device, Ivory and Light Almond color change kits included.

**Color:** **N/A** White, Ivory, Light Almond

**UPC Code:** 07847728238

**Country Of Origin:** China

## Technical Information

### Product Features

**Action:** Standard ON/OFF

**Available Color Kits:** Ivory-I Wht-W Gry-G Blk-E Brwn-B Light Almond-T, R-Red

**Color:** White, Ivory, Light Almond

**Color Change Kit:** IPKIT Series

**Frequency:** 60 Hz

**Light:** LED Locator Light

**Load Rating:** 1200VA

**Load Type:** Electronic 0-10VDC Fluorescent

**Ordering Notes:** Incl White, Ivory and Light Almond Color Kit

**Preset:** Preset

**Protection:** Radio/TV Filter

**Standards and Certifications:** UL/CSA

**Style Name:** IllumaTech

**Switch Type:** Single-Pole & 3-Way

**Type:** Slide

**Voltage:** 120/277 VAC

**Wallplate:** Order Separately

**Warranty:** 5-Year Limited

## SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

