


# Solenoid coil BMSFW-120/60-CSA

Part number: 104080

FESTO



## Data sheet

Feature	Value
Assembly position	Any
Switching position indicator	No
Min. pickup time	10 ms
Duty cycle	100%
Power factor $\cos \{\phi\}$	0.7
Characteristic coil data	120 V AC: 60 Hz, pick-up power 10 VA, holding power 8 VA
Permissible frequency fluctuation	+/- 5 %
Permissible voltage fluctuation	+/- 10 %
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Protection class	IP65
Ambient temperature	-5 ... 40 °C
Authorization	CSA (OL)
Max. tightening torque, plug socket	0.4 Nm
Product weight	55 g
Electrical connection	Plug vanes for MSSD-F 3-pin
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper