

# Suction cup holder ESH-HCL-4-QS

Part number: 189229

FESTO



## Data sheet

Feature	Value
Height compensator for suction-cup holder	20 mm
Volume	1.78 cm <sup>3</sup>
Assembly position	Vertical
Design structure	Vacuum connection at top with height compensation
Correlation to suction-cup holder	Size 4
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	0 ... 60 °C
Product weight	47 g
Mounting type	with lock nut
suction cup mounting	M6
Vacuum connection	QS-6
Materials note	Conforms to RoHS
Material seals	NBR Steel
Material bracket	POM Heat-treatment steel High alloy steel