

## Cat6a Straight-Through Modular In-Line Snap-In Coupler (RJ45 F/F), TAA

MODEL NUMBER: **N235-001-6A**



### Description

Strengthen your high-speed network with Tripp Lite's [N235-001-6A](#) Cat6a Straight-Through Modular In-Line Snap-In Coupler. It connects two Cat6a patch cords to create one longer cable, and its keystone design is perfect for convenient feed-through patching when used with a standard data wallplate (such as Tripp Lite's [N042-001-WH](#)). Built for ultra-fast performance, this is an ideal coupler when setting up premise wiring, voice/data networking, telecommunications and Ethernet connections.

Compatible with all Cat6a cables, regardless of what size wire they use, the [N235-001-6A](#) features straight-through wiring and 50-pin gold-plated contacts designed to resist corrosion. The durable, high-impact polycarbonate housing resists scratching and is colored white to blend in with any color scheme. This coupler is UL-listed and meets all requirements for EIA/TIA Category 6A compliance. It's also backward compatible with Cat6, Cat5e and Cat5 LANs.

### Features

Strengthens Your High-Speed Network

- Ideal for premise wiring, voice/data networking, telecommunications and Ethernet connections
- Connects 2 Cat6a patch cables for a longer cable run
- Keystone design for easy snap-in installation in standard data wallplates (such as Tripp Lite's [N042-001-WH](#))
- Compatible with all Cat6a cables
- Backward compatible with Cat6, Cat5e and Cat5 LANs

Superior Construction for Superior Performance

- Features straight-through wiring

### Highlights

- 50-pin gold-plated contacts on RJ45 jacks
- Heavy-duty polycarbonate housing
- Keystone design for use with standard data wallplate
- Compatible with all Cat6a cables
- Backward compatible with Cat6, Cat5e and Cat5 LANs

### Package Includes

- [N235-001-6A](#) Cat6a Straight-Through Modular In-Line Snap-In Coupler (RJ45 F/F)



- 50- $\mu$ inch gold-plated contacts resist corrosion and improve conduction
- Durable, scratch-resistant polycarbonate housing
- White coloring blends into any color scheme
- UL-listed
- Meets all EIA/TIA Category 6A requirements

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

MODEL TEXT	
Key Benefit	Connects two Cat6a cables to create one longer cable. Provides feed-through patching with standard data wallplates. Ideal for premise wiring, telecommunications, data networking and Ethernet connections.
PHYSICAL	
Color	White
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Relative Humidity	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>