

Threaded nipple fitting CRCN-M5-PK-2

Part number: 30985

FESTO



Data sheet

Feature	Value
Nominal size	1.5 mm
Type of seal on screw-in stud	Sealing ring
Container size	10
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Food-safe	See Supplementary material information
Ambient temperature	0 ... 60 °C
Product weight	1.8 g
Pneumatic connection, port 1	Male thread M5
Pneumatic connection, port 2	for tubing, 3mm outside diameter
Materials note	Conforms to RoHS
Material housing	High alloy steel, non-corrosive
Material of threaded seal	FPM Stainless steel