

Datasheet

ENGLISH

RS Pro LDM Distance Meter - RSLDM-35H

RS Stock No:126-8820



± 1.5 mm Accuracy Battery Life Up to 4000 Display Type LCD Imperial or Metric Both Laser Class Class 2 635 nm Laser Wavelength Measurement Range 0.05 to 35 m Model Number (p) RSLDM-35H Power Source Battery Weight 100 g

RS Pro LDM distance meters designed for quick, non-contact measurement of areas and volumes of rooms, heights, distances and angles. The device allows direct and indirect measurements where access to the target is difficult.

Features and Benefits

- Immediate or long-term (tracking) measurement of the distance to the target (length)
- Angle measurement
- Indirect distance measurements
- Area and volume determination
- Calculations
- Determination of the maximum and minimum values
- Addition and subtraction of indications
- Automatic storage of the last 20 measurement results
- Laser pointer targets
- LCD display with backlight
- Battery status indicator
- · Automatic shut off
- Automatic device off after 3 min of inactivity
- IP54

