

Sealing ring OK-3/4

Part number: 531775

FESTO



Data sheet

Feature	Value
Based on the standard	ISO 16030
Container size	1
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-10 ... 60 °C
Manual tightening at ambient temperature	Yes
Nominal tightening torque	35 Nm
Tolerance for nominal tightening torque	± 10 %
Product weight	1 g
Materials note	Free of copper and PTFE Conforms to RoHS