

Datasheet

Automatic Centre Punch

Art. No.	Length mm	Shank - Ø mm	Striking force		Weigth g
			min N	max N	
430 129	95	11	20	50	30
439 129	Spare pin 3,5 mm				
430 130	125	14	60	130	65
439 130	Spare pin 4,0 mm				
430 131	130	17	180	250	105
439 131	Spare pin 6,0 mm				

Machine steel

rugged self striking mechanism

activated by downward pressure

precision design

replaceable hardened pin

impact force adjustable

nickel plated finish