



# Service unit FRC-3/8-D-5M-MIDI-NPT

Part number: 173856  
Classic

FESTO

Filter/regulator/lubricator combination, 5 µm filter, with metal bowl guard. With manual condensate drain.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



## Data sheet

Feature	Value
Size	Midi
Assembly position	Vertical
Condensate drain	manual momentary-contact
Grade of filtration	5 µm
Working pressure	1 ... 16 bar
Pressure regulation range	0,5 ... 12 bar
Standard nominal flow rate	1,700 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Air purity class at output	Compressed air to ISO 8573-1:2010 [6:8:-] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	1,440 g
Mounting type	Optional Line installation With mounting bracket
Pneumatic connection, port 1	NPT3/8-18
Pneumatic connection, port 2	NPT3/8-18
Materials note	Conforms to RoHS
Material housing	Zinc die-casting
Material bowl	PC