



Pressure booster DPA-40-16-CRVZS2

Part number: 552929

FESTO



Data sheet

Feature	Value
Piston diameter	40 mm
Volume	2 l
Assembly position	Any
Design structure	Twin-piston pressure booster with air reservoir with pressure gauge with non-return valve
Pressure gauge	with pressure gauge
Output pressure 2	4.5 ... 16 bar
Working pressure	2.5 ... 8 bar
Pressure regulation range	4.5 ... 16 bar
Inlet pressure 1	2 ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:3:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	5 ... 60 °C
Ambient temperature	5 ... 60 °C
Product weight	4,400 g
Mounting type	With slot nuts
Pneumatic connection, port 1	QS-10
Pneumatic connection, port 2	KD4
Pneumatic connection, port 3	Silencer
Materials note	Conforms to RoHS
Material of air reservoir	High alloy steel, non-corrosive