


Pressure gauge PAGN-26-1M-P10

Part number: 563736

FESTO



Data sheet

| Feature | Value |
|------------------------------------|-------------------------------|
| Indicating range [MPa] | 0 ... 1 MPa |
| Nominal size of pressure gauge | 26 |
| Design structure | Bourdon-tube pressure gauge |
| Mounting type | Line installation |
| Operating medium | Inert gases Neutral fluids |
| Working pressure | 0 ... 1 MPa |
| Alternating load factor | 0.66 |
| Measurement accuracy class | 4 |
| Protection class | IP43 |
| Medium temperature | -20 ... 60 °C |
| Ambient temperature | -20 ... 60 °C |
| Materials note | Conforms to RoHS |
| Position of connection | Rear side central |
| Pneumatic connection | Cartridge 10 mm |
| Materials in contact with media | Brass |
| Material of threaded plug | Brass |
| Material housing | PA |
| Material screen | PS |
| Housing color | Black |
| Product weight | 15 g |
| Note on operating and pilot medium | No acetylene No oxygen |