



# Pressure gauge PAGN-26-232P-P10

Part number: 563731

FESTO



## Data sheet

Feature	Value
Indicating range [psi]	0 ... 232 psi
Nominal size of pressure gauge	26
Design structure	Bourdon-tube pressure gauge
Mounting type	Line installation
Operating medium	Inert gases Neutral fluids
Working pressure	0 ... 232 Psi
Alternating load factor	0.66
Measurement accuracy class	4
Protection class	IP43
Medium temperature	-20 ... 60 °C
Ambient temperature	-20 ... 60 °C
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	Cartridge 10 mm
Materials in contact with media	Brass
Material of threaded plug	Brass
Material housing	PA
Material screen	PS
Housing color	Black
Product weight	15 g
Note on operating and pilot medium	No acetylene No oxygen