

# Non-return valve HB-1/8-QSM-5/32-U

Part number: 190858

FESTO

Flow rate from the QS plug connector to the male thread.  
This type is suitable for vacuum.



## Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	QS-5/32
Pneumatic connection, port 2	NPT1/8-27
Mounting type	Threaded
Working pressure	-1 ... 10 bar
Ambient temperature	0 ... 60 °C
Material housing	Brass
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Product weight	12 g
Materials note	Conforms to RoHS