



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## C25 Definite Purpose Control Contactor

**C25DNC330BY232-GL**

**UPC:**786685694818

### Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

**Weight:**1.3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Accessories:** Mounting plate
- **Auxiliary Contact:** Pressure plate
- **Coil Voltage:** 208-240 Vac, 50/60 Hz
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Open
- **Number Of Poles:** Three-pole
- **Series:** D1
- **Terminals:** Screw
- **Type:** Non-reversing

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNC330BY232-GL](#)

### Certifications:

- UL Listed file E1491 (Guide Number NLDX2)
- CSA Certified

### Product compliance:

- RoHS Compliant



- CE Marked

---

© 2016 Eaton. All rights reserved.