

Han® S 200 FC CRT 50 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 7264
Specification	Han® S 200 FC CRT 50 mm²
HARTING eCatalogue	https://b2b.harting.com/09930007264

Identification

Category	Contacts
Series	Han® S
Identification	Han® S 200
Type of contact	Crimp contact
Description of the contact	Female contact

Version

Manufacturing process	Turned contacts
Details	Using of rubber sleeve is imperative! Please order separately.

Technical characteristics

Conductor cross-section	50 mm²
Conductor cross-section	AWG 1/0
Rated current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	46.2 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140188884
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors