



Powering Business Worldwide

pe.eaton.com

Definite Purpose Non-Reversing Contactor

C25DND330B-GL

UPC:786685627625

Dimensions:

- **Height:** 2.5 IN
- **Length:** 3.5 IN
- **Width:** 3.5 IN

Weight:1.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 208-240 Vac at 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame:** 15-50A, two- or three-pole
- **Number Of Poles:** Three-pole
- **Special Features:** Global ratings
- **Terminals:** Screw/pressure plate and quick connect terminals (side-by-side)

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25DND3 3D Model Xchange](#)
- [C25DND3 2D PDF](#)
- [C25DND3 2D Drawing Xchange](#)
- [C25DND3 AutoCAD 2D Footprint](#)
- [C25DND3 AutoCAD 2D Footprint \(mm\)](#)
- [C25DND3 3D Inventor](#)
- [Eaton Specification Sheet - C25DND330B-GL](#)

Certifications:

- CSA Certified



Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.