



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## C25 Definite Purpose Control Contactor

C25DND3302C-GL

UPC:786685696164

### Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

**Weight:**1.3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Accessories:** Mounting plate
- **Auxiliary Contact:** Pressure plate quick connect (side-by-side)
- **Coil Voltage:** 480 Vac
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Open
- **Number Of Poles:** Three-pole
- **Options:** Global listed
- **Series:** D1
- **Terminals:** Screw
- **Type:** Non-reversing

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25DND3 2D PDF](#)
- [C25DND3 3D Model Xchange](#)
- [C25DND3 3D Inventor](#)
- [C25DND3 AutoCAD 2D Footprint \(mm\)](#)
- [C25DND3 2D Drawing Xchange](#)
- [C25DND3 AutoCAD 2D Footprint](#)



- [Eaton Specification Sheet - C25DND3302C-GL](#)

**Certifications:**

- CSA Certified
- UL Listed file E1491 (Guide Number NLDX2)

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.