



Powering Business Worldwide

pe.eaton.com

C25 Definite Purpose Control Contactor

C25DNF325T461-GL

UPC:786685698861

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

Weight:1.3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Accessories:** Mounting plate
- **Fuse Block:** Class T, 600V, 30A
- **Auxiliary Contact:** Quick connect (side-by-side)
- **Coil Voltage:** 24 Vac, 50/60 Hz
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Open
- **Number Of Poles:** Three-pole
- **Options:** Global listed
- **Series:** D1
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNF325T461-GL](#)

Certifications:

- CSA Certified
- UL Listed file E1491 (Guide Number NLDX2)



Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.