



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25HNE3120AC

UPC:782114182574

Dimensions:

- **Height:** 7.17 IN
- **Length:** 5.94 IN
- **Width:** 3.54 IN

Weight:8.5 LB

Notes:Resistive Load rating per pole. Auxiliary contact includes standard pressure plate terminals.

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 120A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Contact Configuration:** 1NO, 1NC
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 120A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 140A
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25HNE3120AC](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data



