



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH2L125RP

UPC:782114190487

Dimensions:

- **Height:** 3.13 IN
- **Length:** 9.5 IN
- **Width:** 4.5 IN

Notes: Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main lug only
- **Amperage Rating:** 125A
- **Box Size:** 6r
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 2
- **Number Of Poles:** Four-pole
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #1-4/0 AWG

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)



- [Eaton Specification Sheet - CH2L125RP](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.