Best Designed J-Hook for

Modern Cable Installs!

Snap-Lock

Opened

HPH J-Hooks

The High Performance Hybrid J-Hooks are 2" wide, designed with a reusable Snap-Lock latch for securing cable, and are UL listed and Plenum rated.

Features

- Wide base support 2"
- Industry leading bend radius
- Snap-Lock latch firmly secures cables
- Eliminates the use of Cable Ties/Velcro Ties
- Made with easy slide, slick, burr free surface
- No pressure points
- Light-weight
- Flush mount for easy installation
- Economical

Technical

- cULus Listed
- Plenum Rated
- RoHS Compliant
- TIA Compliant

Sizing

Snap-Lock Closed The HPH J-Hooks come in four sizes and are available assembled to the most common fasteners:

- HPH16 (1")
- HPH32 (2")
- HPH48 (3")
- HPH64 (4")

See reverse side for part numbers, ordering information, cable capacities, and special order custom assemblies





California, USA

Phone: 805.384.2777 / 800.749.5783 • Fax: 800.749.5784

www.platinumtools.com

We Make Connections EZ!™

TIA Compliant

Bend Radius



How to Order:







Batwing HPH
N HPH16W-25
25/Box
N HPH32W-25
25/Box
N HPH48W-25
25/Box
N HPH64W-25
25/Box
N N

Note: Cable Capacity refers to the number of cables per J-Hook

Special Order Information

"XX" stands for the size of the HPH J-Hook. Sizes range from 1"(16), 2"(32), 3"(48), and 4"(64). Part numbers are for special order purposes only. For more information, please contact Platinum Tools.

Example: HPH32BC-25

HPH J-Hook, size 32 (2"), Steel Beam Clamp, Swivels 360°



HPHXXBC-25 Steel Beam Clamp, swivels 360°



HPHXXPA-25 Right Angle Powder Actuated



HPHXXACSSBC-25 Spring Steel Beam Clamp, swivels 360°



HPHXXSSBCF-25 Spring Steel Beam Clamp Fixed



HPHXXVO-25 Vertical Overhang for "C" Purlin



HPHXXACFM58-25 Hammer-On Beam Clamp, swivels 360°



HPHXXAO-25 Angled Overhang for "Z" Purlin



HPHXXBCF-25 Steel Beam Clamp Fixed



HPHXXHOK58-25 Hammer-On Beam Clamp, fixed

California, USA

Phone: 805.384.2777 / 800.749.5783 • Fax: 800.749.5784