



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E50 Heavy Duty Factory Sealed 6P+ Limit Switch

**E50SA6P12**

**UPC:**782113135618

### Dimensions:

- **Height:** 3.58 IN
- **Length:** 1.54 IN
- **Width:** 1.58 IN

**Weight:**2.1188 LB

**Notes:**Switch body only; full switch requires a switch body and operating head.

### Warranties:

- 1 year

### Specifications:

- **Connection:** 12 Ft. ( 3.7m ) Cable
- **Contact Rating:** 10A at 240Vac, 1A at 250Vdc
- **Cable Type:** SOOW-A
- **Contact Configuration:** 1NO-1NC
- **Cord Length:** 144 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** -29° to 221°F (-34° to 105°C)


### Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SA6P12](#)

### Certifications:

- CSA Certified
- UL Recognized

### Product compliance:



- CE Marked

---

© 2016 Eaton. All rights reserved.