



ENGLISH

RS PRO 2Kw Box Fan Heater

144-362

Built to last, the Climate King series of Premium Quality Fan Heaters has been subjected to rigorous testing to ensure every detail provides a superior performance.

From the high efficiency stainless steel heating element and aluminium fan blade to the insulated ergonomic handle and robust controls, everything screams quality. The dual protection against overheating and built in thermostat provide stable power whilst its waterproof IPX4 rating means it can be used in damp conditions making it perfect for use in workshops, garages, greenhouses and building sites etc



Additional features include a rust resistant powdered casing, a time-delay feature that allows the fan to cool the machine after the heating element has been turned off and 2 heating levels plus a fan only mode. Combined with the variable thermostat and the built in handle, this means you can achieve the temperature you require in the place you want it. And there is no delay; every Climate King Premium Heater comes complete with an appropriate power cord in the box so you can plug in and start heating immediately.

A 12 month labour and parts warranty is also included.

FEATURES : MODEL HCK-BX2UK

1. Electrical supply : 240V/50Hz, 13A
2. Heating output in 2 level: 1.0Kw / 2 Kw
3. Heating element: Stainless steel
4. Air out put: 186 m³/h
5. Heating area: upto 40 m³
6. With Aluminium fan blade
7. Adjustable thermostat for comfort
8. High efficiency stainless element provides durability and safety

9. Double overheating protection for added safety
10. With time-delay to help the heater cool quickly
11. With sensor thermostat so you can select the temperature of the Environment
12. Insulated handle for safety
13. Free standing & portable type
14. Waterproof class IPX4

Warning :

The heater element will be hot but will not glow visibly due to the high airflow over the element

Dimensions : 230x198x320mm

Weight Net : 3.5Kg Gross 4.0KG