



ENGLISH

Datasheet

Stock No: 361-838

RS Pro White, 2491X Equipment Wire, 1.5 mm² CSA , 750 V 15 A 15 AWG, 100m



Product Details

2491X

A plain copper stranded conductor covered by a PVC insulated sheath. These flexible wires are intended for use in internal wiring applications in electrical and electronic equipment, or runs within covered ducts, conduits.

Features & Benefits:

- * Flexible class 5 conductors
- * BS6004 Conductors
- * Plain annealed copper conductors

Note

The RS Brand range of products has been certified by engineers as offering comparable quality to that of leading brands without the premium price tag

Specifications

Cross Sectional Area	1.5 mm ²
Sheath Colour	White
Core Strands	30/0.25 mm
Insulation Material	PVC
Outer Diameter	3.4mm
Length	100m
Number of Strands	30
Current Rating	15 A
Voltage Rating	750 V
Size of Strands	0.25 mm
American Wire Gauge	15 AWG
Conductor Material	Annealed Copper
Type	2491X
Shield Type	Unshielded
Insulation Wall Thickness	0.7mm
European Harmonised Code	H07V-K
Cable Shape	Single Core