

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm² and 4 - 6 mm² (light green, yellow), packed in a serial storage box

Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4046356452526

Technical data

Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.1 mm ²
Max. cross section	0.4 mm ²
AWG min	26
AWG max	22
Designation	Crimping position 2
Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10
Weight	66 g
Min. cross section	0.1 mm ²
Max. cross section	6 mm ²

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>