
SERIES BCHP LOW PRESSURE CALIBRATION PUMP Vacuum or Pressure, Generates up to 870 psi (60 bar)



The **SERIES BCHP** Low Pressure Calibration Pump is able to generate pressure and vacuum for adjusting or calibrating pressure gauges, transmitters, or switches. The pump is hand operated and has a pneumatic pressure range of -28 to 870 psi (-0.95 to 60 bar).

FEATURES/BENEFITS

- · Dual pressure ports for ease of use
- · Fine adjustment valve ensures precise measurements

APPLICATIONS

- · Instrument calibration
- Laboratories
- Production areas

MODEL CHART

Model	Description
BCHP-1	Calibration test pump
BCHP-KIT	Test pump with 1/4" NPT connections, fine volume adjustment tool and
	case

SPECIFICATIONS

Media: Air.

Output Ranges: -28 in Hg to 870 psi (-0.95 to 60 bar). Process Connections: 1/4" female BSP Gage Connection: 1/2" female BSP. Materials: Anodized aluminum, brass, and ABS. Weight: 8.4 lb (3.8 kg).

ACCESSORIES		
Model	Description	
A-BCHP-CASE	Case for BCHP-1	
A-BCHP-NPT	1/4" BSP to 1/8" NPT, 1/4" NPT, 3/8" NPT and 1/2" NPT converter	
	set for test connection	
A-BCHP-VAT	Fine volume adjustment tool	

USA: California Proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov