

# Replacement die - CRIMPFOX-M SC 6/DIE - 1212085

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.5 - 6 mm<sup>2</sup>, packed in a serial storage box

## Key Commercial Data

Packing unit	1 STK
GTIN	4 046356 454551
GTIN	4046356454551

## Technical data

### Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

### General

Color	black
Compression	B crimp
Type of contact	Slip-on sleeve
Designation	Crimping position 1
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	22
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	16
AWG max	14
Designation	Crimping position 3
Min. cross section	4 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	12

# Replacement die - CRIMPFOX-M SC 6/DIE - 1212085

## Technical data

### General

AWG max	10
Weight	74 g
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>