



Dual Flat-Panel Rail Wall Mount for 10” to 24” TVs and Monitors

MODEL NUMBER: **DMR1024X2**

Description

The VESA-compliant DMR1024X2 Dual Flat-Panel Rail Wall Mount allows you to mount two flat-panel televisions, monitors or other displays on the wall in either portrait or landscape mode. Recommended for video walls, menu boards and other display applications in restaurants, bars, airports, hotels, offices and boardrooms, the low-profile mount fits most flat-panel displays from 10 to 24 inches.

Dual displays attach to VESA mounts that can slide closer or further apart along the rail for optimal viewing. The rail is concealed behind the displays for a sleek, professional appearance. Included cable guides attach to the rail to keep power cords out of the way.

Durable steel construction supports up to 18 pounds per VESA mount. Mounting hardware is included. Conforms to VESA-compliant displays with either of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Mounts 2 Televisions or Monitors to the Wall

- Fits most flat-panel TVs, monitors and other displays from 10 to 24 in.
- Ideal for video walls, menu boards and other display applications in restaurants, bars, airports, hotels, offices and boardrooms
- Designed for portrait or landscape mounting

Innovative Rail Design

- VESA mounts adjust independently along rail
- Rail conceals behind displays for sleek, professional appearance
- Cables attach to rail to prevent tangles and clutter
- Adjustable mounting rails match up with off-center wall studs
- Wall-mounting hardware included

Durable Steel Construction

- Supports up to 18 lb. per VESA mount

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

Highlights

- Fits most flat-panel displays from 10 to 24 in.
- Designed for portrait or landscape mounting
- VESA mounts adjust independently along rail
- Durable steel construction
- Supports up to 18 lb. per VESA mount

Package Includes

- Wall rail
- (2) VESA mounts
- (8) M4 x 12 screws
- (8) M4 x 30 screws
- (8) Spacers
- (3) Cable guides
- (5) Anchor bolts
- (5) Concrete anchors
- (5) Washers
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

MODEL TEXT	
Key Benefit	Low-profile rail mount hangs 2 flat-panel televisions, monitors or other displays on the wall. Recommended for video walls, menu boards and other displays in restaurants, bars, airports, hotels, offices and boardrooms.
PHYSICAL	
Mounting Location	Wall
Unit Weight (lbs.)	5.08
Unit Weight (kg)	2.30
Material of Construction	Steel
Color	Silver
Screen Size Compatibility (in.)	10 to 24
Screen Size Compatibility (cm)	25.4 x 60.96
VESA Pattern (mm)	75x75; 100x100
Motion	Fixed
Degrees of Motion	20 Swivel, 360 Rotate, -15/+15 Tilt
Min/Max Arm Extension (in.)	3
Min/Max Arm Extension (cm)	7.62
Maximum Weight Capacity (lbs.)	18
Maximum Weight Capacity (kg)	8
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>