

Dual-Monitor Desktop Mount Stand for 13" to 27" Flat-Screen Displays

MODEL NUMBER: **DDR1327SDD**

Description

The VESA-compliant DDR1327SDD Dual Flat-Screen Monitor Desktop Mount Stand mounts two flat-screen monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Recommended for home or office, the DDR1327SDD fits most flat-panel displays from 13 to 27 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -45° to +45° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each VESA mount supports up to 26 pounds. The durable steel frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with either of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Mounts 2 Flat-Screen Monitors on a Sturdy Base

- Fits most flat-panel TVs, monitors and other displays from 13 to 27 in.
- Frees up valuable workspace on your desk, table or workstation
- Mounting arms adjust independently for viewing angle
- Ideal for home or office use

Convenient One-Touch Adjustment

- 180° swivel and -45° to +45° tilt capability provide comfortable viewing
- Full 360° rotation for viewing in portrait or landscape orientation

Durable Steel Construction

- Each mount supports up to 26 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Mounting hardware included

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- Rotates 360° for viewing in portrait or landscape orientation
- 180° swivel and -45° to +45° tilt for wide range of motion
- Supports up to 26 lb. per VESA mount

Package Includes

- Pole
- Base
- (2) Mounting arms
- Locking head assembly
- Pole cable guide
- Base collar
- (2) VESA plate assemblies
- (2) Arm cable guides
- (2) End caps
- (8) Washers
- (18) Screws
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual



MODEL TEXT	
Key Benefit	Full-motion desktop stand mounts 2 flat-screen monitors on independently adjustable arms and a single base to free up valuable space on your desk, table or workstation. Recommended for home or office use.
PHYSICAL	
Mounting Location	Desktop
Unit Dimensions (hwd / in.)	18.11 x 31.69 x 10
Unit Dimensions (hwd / cm)	46.0 x 80.5 x 25.4
Unit Weight (lbs.)	10.56
Unit Weight (kg)	4.79
Material of Construction	steel
Color	Black
Screen Size Compatibility (in.)	13-27
Screen Size Compatibility (cm)	33.2 x 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-45/+45 Tilt; 180 swivel; 360 rotate
Maximum Weight Capacity (lbs.)	26
Maximum Weight Capacity (kg)	12
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>