

## Heavy-Duty Power Extension Cord, 15A, 14 AWG (IEC-320-C14 to IEC-320-C13), Orange, 6 ft.

MODEL NUMBER: P005-006-AOR



### Highlights

- Easy-to-identify orange SJT jacket and fully molded orange ends
- Flexible 14 AWG wire for easy routing
- 250V/15A rating
- UL-listed
- Also recommended for replacing lost or old power cord

### Package Includes

- P005-006-AOR Heavy-Duty Power Extension Cord, Orange, 6 ft.

### Description

The P005-006-AOR Heavy-Duty Power Extension Cord is recommended for replacing a lost or worn-out power cord or extending your current power connection by six feet. It features an orange SJT jacket and fully molded orange ends, allowing you to easily identify your connections in a crowded workstation. A C14 male connector on one end and a C13 female connector on the other let you attach computers, printers, scanners, power supplies, monitors and other compatible hardware. This six-foot 15A cord supports voltages up to 250V. It's UL-listed and features a flexible SJT jacket and 14 AWG wire for easy routing through tight areas.

### Features

Safe, Reliable Power Solution

- Connects hardware with C13/C14 power connectors
- Ideal for replacing an old or lost cord
- Extends current power connection by 6 ft.

Color-Coded Cable and Connectors

- Colored orange for easy identification in crowded rack or workstation

Optimum Construction

- 14 AWG wire
- Flexible SJT jacket
- 250V/15A rating
- UL-listed



## Specifications

MODEL TEXT	
Key Benefit	Color-coded cable connects hardware, such as computers, printers, scanners, power supplies and monitors, with C13/C14 power connectors. Or extends your current power connection by 6 ft.
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Cable Length (cm)	182.88
PHYSICAL	
Color	Orange
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>